

التاريخ: 05/08/2021

السادة: ..... المحترمين

تلفون: .....

فاكس: .....

(Q239.2021)

رقم / الاستدراج :

Cross-Linking  
Machine

الموضوع : عروض اسعار

إشارة إلى الموضوع اعلاه الرجاء تزويدنا بأسعار اللوازم التالية (بالدولار) شامل لضريبة القيمة المضافة والتوصيل للجامعة العربية الأمريكية:

#	اسم الصنف	الوحدة	الكمية	السعر	اجمالي تكلفة البند
1	Cross-Linking Machine: مرفق الوصف في الصفحة 3,2	EACH	1		
				المجموع الكلي	

شروط الاستدراج

الموافق: 12/08/2021

الخميس

1- يرجى العلم ان اخر موعد لتسليم العروض هو يوم

2- الاسعار شاملة لضريبة القيمة المضافة.

3- ضرورة تحديد مدة التوريد من تاريخ استلام امر الشراء، و في حال عدم الالتزام يتم فرض غرامة تأخير .

4- ختم وتوقيع المورد المعتمد على هذا النموذج، وكتابة رقم الاستدراج واسم الشركة كما هو مسجل لدى الضريبة على الظرف.

5- لا تقبل العروض الا بالظرف المختوم.

6- للمراجعة والاستفسار بخصوص المواصفات يرجى الاتصال على هاتف 042418888 رقم داخلي 1478 او فاكس 042510972 أو بريد

الالكتروني manal.daraghmah@aaup.edu

7- لمشاهدة العطاءات والاستدراجات، يرجى الدخول الى الرابط <http://www.aaup.edu/Tenders>

مع الاحترام

مدير دائرة اللوازم و المشتريات

أ. حسن ربايعه



3/1

### **Cross-Linking Machine:**

(UV device with a single or homogenized cluster LED for Cross-linking treatment in order to strengthen the collagen fibers in the cornea)

**Brand name.**

**3 years' warranty, 10 years' availability spare parts.**

**Origin: USA, EURO, Japan**

- \* Timer and Monitor to observe all procedure steps.
- \* Built in real time camera with Eye Tracking.
- \* Dual Aiming beam assisted focusing.
- \* UVC source: Single LED for UV-A rays.
- \* Wavelength: ~370nm.
- \* UV Power : 3 to 11 mW/cm2 (User Programmable).
- \* Variable beam diameter for different corneal diameters: 1 - 11 mm.
- \* Motorized Fine Focus.
- \* Continuous and Pulsed Modes.
- \* Integrated Pachymeter is preferred.
- \* Touch screen operation.
- \* Video assisted procedure.
- \* Self-calibration of UVA irradiation intensity.
- \* Control foot pedal is preferred.
- \* Rigid Mobile Floor Stand Mount.
- \* Rotatable Arm.
- \* Power supply: 230V, 50/60Hz.

### **Safety and Training:**

- \* Preferred to be FDA or CE approved product.
- \* User and service manual in English.
- \* Full application training for the operators on site.
- \* List of important spare parts and accessories with their part numbers and costing.
- \* Recommended spare parts to be available at least for 10 years.

السعر يشمل التوريد والتركيب ويجب أن يتم توضيح جميع متطلبات التركيب في عرض السعر من ملحقات ومتطلبات

3/2



❖ Kindly your offer will not be taken into our consideration if you don't fill below table.

<b><u>Cross-Linking Machine</u></b>	<b>Yes/No</b>	<b>Comment</b>
<b>Manufacture .</b>	Manufacture	
<b>Model .</b>	Model	
<b>Origin: USA , Europe , Japan .</b>	Origin	
<b>Delivery time .</b>	Weeks	
<b>3 years Full warranty .</b>	Yes/No	
<b>Brand name .</b>	Yes/No	
Timer and Monitor to observe all procedure steps	Yes/No	
Built in real time camera with Eye Tracking	Yes/No	
Dual Aiming beam assisted focusing	Yes/No	
UVC source : Single LED for UV-A rays	Yes/No	
Wavelength : ~370nm	Yes/No	
UV Power : 3 to 11 mW/cm2 (User Programmable)	Yes/No	
Variable beam diameter for different corneal diameters: 1 - 11 mm	Yes/No	
Motorized Fine Focus	Yes/No	
Continuous and Pulsed Modes	Yes/No	
Integrated Pachymeter is preferred	Yes/No	
Touch screen operation	Yes/No	
Video assisted procedure	Yes/No	
Self-calibration of UVA irradiation intensity	Yes/No	
Control foot pedal is preferred	Yes/No	
Rigid Mobile Floor Stand Mount	Yes/No	
Rotatable Arm	Yes/No	
Power supply : 230V, 50/60Hz.	Yes/No	
<b>Preferred to be FDA or CE approved product</b>	Yes/No	
<b>User and service manuals .</b>	Yes/No	
<b>Price include installation with application training in site .</b>	Yes/No	
<b>Complete and Ready to use with all accessories.</b>	Yes/No	
<b>10 years availability for spare parts.</b>	Yes/No	
<b>Date of manufacture not less than 2021.</b>	Yes/No	
في حال وجود أية قطعة ضرورية لتشغيل الجهاز وعمله بشكل كامل وطبيعي غير موضحة يرجى ذكرها وتوضيحها في العرض غير ذلك تلتزم الشركة بتحمل وجود أية نواقص.	Yes/No	

3/3

