

التاريخ 09/06/2022

رقم الاستدراج: Q342.2022

السادة:

تلفون:

إيميل:

استدراج عروض أسعار: الرجاء تزويدنا بأسعار اللوازم التالية شامل لضريبة القيمة المضافة:

BR2122-000

#	اسم الصنف	الوحدة	الكمية	السعر	اجمالي تكلفة البند
1	Ultra low -86 C Deep Freezer المواصفات على الصفحة 2+3	عدد	1		

المجموع الكلي (ش.ض) دولار

ختم وتوقيع المورد:

تعليمات الاستدراج

** آخر موعد لتسليم العروض هو يوم:	الثلاثاء
** الموافق:	14/06/2022
** طبيعة البنود المطلوبة:	Ultra low -86 C Deep Freezer
** بعملة:	دولار
** الأسعار تشمل التوصيل ل:	الحرم الرئيسي - جنين
** نوع التوريد:	توريد كامل
** يرجى إرسال العرض ب:	بالظرف المغلق

شروط الاستدراج:

- ** ضرورة تحديد مدة الكفالة إن وجدت.
- ** ضرورة تحديد مدة التوريد من تاريخ استلام امر الشراء، وفي حال عدم الالتزام يتم فرض غرامة تأخير .
- ** ختم وتوقيع المورد المعتمد على هذا النموذج، وكتابة رقم الاستدراج واسم الشركة كما هو مسجل لدى الضريبة على الطرف.
- ** للمراجعة والاستفسار بخصوص المواصفات يرجى الاتصال على هاتف 042418888 رقم داخلي 1481 أو الرقم 1491
- ** للمراجعة والاستفسار بخصوص المواصفات عن طريق فاكس 042510972 أو بريد الكتروني manal.daraghmah@aaup.edu
- ** لمشاهدة العطاءات والاستدراجات، يرجى الدخول الى الرابط <http://www.aaup.edu/tenders>

مدير دائرة اللوازم و المشتريات



Ultra low -86 C Deep Freezer

Brand name.

Origin: USA, Europe , japan.

For biology and research lab application.

Up right .

Volume: minimum 350 L.

Temp . Range : up to – 86 C .

Shelves : 4 .

Fully programmable microprocessor controlled with membrane keypad and eye level control panel .

Data Logger: Temp-monitoring system with electronic chart recorder

Refrigeration system : Cascade .

Minimum temperature recovery time after door opening.

lockable outer doors and lids are required .

Insulation: polyurethane 135 mm thick.

Must have battery back-up .

Audible and visible alarms for: Temp. High/low, filter check, self-diagnostics, door check, power failure, battery low ,

Smart diagnostics for simpler system diagnostics

Must use CFC-FREE, HCFC-FREE non-flammable refrigerants.

Freezers should have heated air vent and front panel air filter.

Heavy-duty lockable castors.

Noise Level: less than 50 (db).

Freezer must have standard quality test requirements and Electrical safety certified.

With Temperature calibration certificate.

Warranty: 5 years .

Optional:

different size Racks with Boxes.

Online UPS enough for 30 minutes working time .

Air filter .

❖ **Kindly your offer will not be taken into our consideration if you don't fill below table.**

<u>Ultra low -86 C Deep Freezer</u>	Yes/No	Comment
Manufacture	Manufacture	
Model	Model	
Origin: USA, Europe , japan	Origin	
Delivery time	Delivery time	
<u>Warranty : 5 years.</u>	Yes/No	
For biology and research lab application.	Yes/No	
Up right .	Yes/No	
Volume: minimum 350 L.	Yes/No	
Temp . Range : up to – 80 C .	Yes/No	
Shelves : 4 .	Yes/No	

2



Fully programmable microprocessor controlled with membrane keypad and eye level control panel .	Yes/No	
Data Logger: Temp monitoring system with electronic chart recorder	Yes/No	
Refrigeration system : Cascade .	Yes/No	
Minimum temperature recovery time after door opening.	Yes/No	
lockable outer doors and lids are required .	Yes/No	
Insulation: polyurethane 135 mm thick.	Yes/No	
Must have battery back-up .	Yes/No	
Audible and visible alarms for: Temp. High/low, filter check, self-diagnostics, door check, power failure, battery low ,	Yes/No	
Smart diagnostics for simpler system diagnostics	Yes/No	
Must use CFC-FREE, HCFC-FREE non-flammable refrigerants.	Yes/No	
Freezers should have heated air vent and front panel air filter.	Yes/No	
Heavy-duty lockable castors.	Yes/No	
Noise Level: less than 50 (db) .	Yes/No	
Freezer must have standard quality test requirements and Electrical safety certified.	Yes/No	
With Temperature calibration certificate.	Yes/No	
<u>optional:</u>	Yes/No	
different size Racks with Boxes .	Yes/No	
Online UPS enough for 30 minutes working time .	Yes/No	
Air filter .	Yes/No	
10 years availability for spare parts	Yes/No	
Complete and Ready to use with all accessories	Yes/No	
User's and service manual	Yes/No	
Price include installation training in site	Yes/No	
<i>Date of manufacture not less than 2022</i>		

3

